

AAMC Eschenbach Loupes

LED LIGHT LOUPE MOBILUX

The aspherical lens with low distortion. PXM optical resin lens developed by Eschenbach. Scratch-resistant and brightly magnified. Can be used as a stand loupe by using the stand.

Model No.1511-2M, 1511-41M, 1511-5M, 1511-6M Magnification:3X, 4X, 5X, 6X Lens size(mm): φ60, 50 x 75, φ58, φ58



LOUPE MOBILENT

The aspherical lens with low distortion. PXM optical resin lens developed by Eschenbach. Scratch-resistant and brightly magnified. The case has a dustproof, airtight structure. Compact size. Strap Included.

Model No.1710-94, 1710-97, 1710-910S Magnification:4X, 7X, 10X Lens size(mm) :φ35 Weight: 28 g,30 g, 32 g Dimension(mm):52 x 53 x 23



PRECISION FOLDING MAGNIFIERS

The achromatic lens with low aberration. A sturdy case with a matte chrome finish and a black metal frame protects the lens.

Model No.1184-10, 1184-20 Magnification:10X, 20X_ Lens size(mm): φ15, φ17 Lens effective diameter: φ15, φ12 Lens Type: Achromatic lens Weight: 50 g, 52 g



WATCHMAKER'S MAGNIFIER

These loupes have been used by watchmakers and gemologists. Air vent holes are in the frame to prevent the inner lens from fogging up. Lightweight, large diameter, and easy to see. Scratch-resistant.

Model No.1124-3, 1124-5, 1124-7, 1124-10 Magnification:3X, 5X, 7X, 10X Lens size(mm) φ25 Lens Material: PXM Plastic Lens Type:Plano-Convex(3X, 5X, 7X)

Lens Type: Bi-Convex(10X) Dpt.: 12, 20, 27.7, 40

Weight: 4 g Dimension(mm):φ38 x 25





ALFA Mirage Co., Ltd.